



America

# CERTIFICATE

**No. U8 18 05 56257 186****Holder of Certificate: Leica Microsystems CMS GmbH**

Ernst-Leitz-Straße 17-37  
35578 Wetzlar  
GERMANY

**Production****Facility(ies):**

30821

**Certification Mark:****Product:****C US  
Laboratory Equipment****Model(s):****DM2500 LED  
Type: 11888855  
DM2500  
Type: 11888139****Parameters:**

Model:	DM2500 LED
Type:	11888855
Rated voltage:	100-240 V
Rated frequency:	50/60 Hz
Rated power:	40 VA
Protection class:	I

Model:	DM2500
Type:	11888139
Rated voltage:	100-240 V
Rated frequency:	50/60 Hz
Rated power:	190 VA
Protection class:	I

**Tested  
according to:**

UL 61010-1:2012/R:2016-04  
UL 61010-2-101:2015  
CAN/CSA-C22.2 No. 61010-1:2012/U2:2016-04  
CAN/CSA-C22.2 No. 61010-2-101:2015

The product was voluntarily tested according to the relevant safety requirements noted above. It can be marked with the certification mark above. The mark must not be altered in any way. This product certification system operated by TÜV SÜD America Inc. most closely resembles system 3 as defined in ISO/IEC 17067. Certification is based on the TÜV SÜD "Testing and Certification Regulations". TÜV SÜD America Inc. is an OSHA recognized NRTL and a Standards Council of Canada accredited certification body.

**Test report no.:**

028-713134232-000

**Date,** 2018-06-04

Page 1 of 1

