



America

CERTIFICATE

No. U8 17 04 56257 159

Holder of Certificate: Leica Microsystems CMS GmbH

Ernst-Leitz-Straße 17-37
35578 Wetzlar
GERMANY

**Production
Facility(ies):**

30821

Certification Mark:



C US

Product:

**Laboratory Equipment
(microscope)**

Model(s):

DM3 XL

Parameters:

Type reference: 11890018

Rated voltage: 100-240 V

Rated frequency: 50/60 Hz

Rated power: 40 VA

Protection class: I

Hint:

Lamp classification: exempt Group

**Tested
according to:**

UL 61010-1:2012/R:2015-07

CAN/CSA-C22.2 no. 61010-1:2012 + UPD No. 1:2015-07

UPD No. 2:2016-04

The product was voluntarily tested according to the relevant safety requirements noted above. It can be marked with the certification mark above. The mark must not be altered in any way. This product certification system operated by TÜV SÜD America Inc. most closely resembles system 3 as defined in ISO/IEC 17067. Certification is based on the TÜV SÜD "Testing and Certification Regulations". TÜV SÜD America Inc. is an OSHA recognized NRTL and a Standards Council of Canada accredited certification body.

Test report no.:

028-713105274-000

Date, 2017-04-19

Page 1 of 1

