


America

CERTIFICATE

No. U8 042849 0007 Rev. 00

Holder of Certificate: **Leica Microsystems AG**
9435 Heerbrugg
SWITZERLAND

Certification Mark:



C US

Product: **Laboratory Equipment
(Microscopes)**

Model(s): **DM500 (X)**
DM750 (X), DM750 M (X), DM750 P (X)
(X) optional, where (X) can be one or more alphanumeric digits to reflect customer specific version and represent optical accessories and/or different sample holder, not relevant for safety.

Parameters:

Rated voltage:	100–240 VAC
Rated frequency:	50/60 Hz
Rated power	17 W
Protection class:	I

Tested according to: UL 61010-1:2012/R:2019-07
CSA C22.2 No. 61010-1:2012/A1:2018-11

This product was voluntarily tested to the relevant safety requirements referenced on this certificate. It can be marked with the certification mark above. The mark must not be altered in any way. This product certification system operated by TÜV SÜD America Inc. most closely resembles system 3 as defined in ISO/IEC 17067. Certification is based on the TÜV SÜD "Testing and Certification Regulations". TÜV SÜD America Inc. is an OSHA recognized NRTL for USA and a Standards Council of Canada ISO/IEC 17065 accredited Certification body for Canada.

Test report no.: 713304202

Date, 2023-06-30

(Thorsten Siemon)