



America

CERTIFICATE

No. U8 15 04 56257 104

Holder of Certificate: Leica Microsystems CMS GmbH

Ernst-Leitz-Straße 17-37
35578 Wetzlar
GERMANY

Production Facility(ies): 30821

Certification Mark:



C US

Product: Laboratory Equipment
(microscope)

Model(s): DM2700P
DM2700M RL
DB 2700M RL/TL

Parameters:

Rated Voltage:	100-240 VAC
Rated frequency:	50/60 Hz
Rated power:	40 VA
Protection class:	I

Tested according to: UL 61010-1:2012-05
CAN/CSA-C22.2 No. 61010-1:2012-05

The product was voluntarily tested according to the relevant safety requirements noted above. It can be marked with the certification mark above. The mark must not be altered in anyway. This product certification system operated by TÜV SÜD America Inc. most closely resembles system 3 as defined in ISO/IEC Guide 67. Certification is based on the TÜV SÜD "Testing and Certification Regulations". TÜV SÜD America Inc. is an OSHA recognized NRTL and a Standards Council of Canada accredited certification body.

Test report no.: 028-713058561-000

Date, 2015-04-02

Page 1 of 1

